

STEALTH™

DRINKING WATER SYSTEMS

COMPACT IN SIZE,
BIG IN PERFORMANCE



- **STEALTH 100** 100 GPD
- **STEALTH 200** 200 GPD
- **STEALTH 300** 300 GPD

Enjoy PURE HEALTHY WATER


5 STAGE REVERSE OSMOSIS (RO) PROCESS WITH HIGH FLOW BOOSTER PUMP*

- Stage 1** 5 micron polypropylene sediment pre-filter to extract suspended materials such as sediments, insects, asbestos fiber, rust, and particles down to 5 micron.
- Stages 2 & 3** Double carbon block cartridges (2 micron) to absorb chlorine and chlorine byproducts without release of carbon fines.
- Stage 4** High rejection Thin Film Composite (TFC) RO membranes to reject a wide spectrum of impurities including TDS, bacteria, and viruses down to 0.0001 micron. The product water is stored in the optional storage tank, while the reject water is automatically flushed down the drain.
- Stage 5** GAC Cartridge is used to remove dissolved gases, bad taste and odor from product water. This is the final polishing stage prior to consumption.

*Using standard 10" cartridges & residential size membranes.

STANDARD FEATURES

	100	200	300
NSF listed 100 GDP high rejection TFC membrane	1	2	3
NSF listed high flow booster pump w/trans. (110v/60hz or 220v/50hz)	1	1	1
Automatic shut-off valve (when tank is full)	✓	✓	✓
Powder coated, heavy duty steel frame	✓	✓	✓
Color coded tubing 3/8" for easier installation	✓	✓	✓
Built-in pressure gauge 0-160 psi, glycerin filled	✓	✓	✓
Complete installation kit and instruction manual	✓	✓	✓
Attractive long reach chrome faucet	✓	✓	✓
High quality components with FDA/NSF approval	✓	✓	✓
1-Year limited warranty	✓	✓	✓
Automatic high pressure switch	✓	✓	✓
Automatic low pressure switch	✓	✓	✓
Number of persons served	25-50	50-100	150-250



OPTIONS FOR **STEALTH**™

Consult our sales department for more information

1. In-line UV lamp stainless steel 2.0 GPM
2. Stainless steel, colored, or designer faucets
3. Manual or automatic flushing device
4. 11, 20 or 34 gallon storage tank
5. Install TDS monitor
6. Delivery pump

MODEL	PRODUCTION		ELECTRICAL	PRODUCT RECOVERY	TDS REJECTION	SHIPPING WEIGHT	SHIPPING DIMENSIONS
	GPD	LPH				System	System
STEALTH - 100	100	15.75	110V-60HZ OR 220V-50HZ	30-35%	99%	30 LBS	17.5 x 18.5 x 10.5
STEALTH - 200	200	31.5		35-40%		32 LBS	
STEALTH- 300	300	47.3		40-45%		34 LBS	

DISTRIBUTED BY

